

# AutoScan-DS200+

**Unmatched Scan Speed** 



Email: sales@shining3d.com Tel: +86 571 82999050 Web: www.shining3d.com



### **Color Texture Capturing Function**

Capture the complete plaster model and marks drawing by hand clearly, the fine details offers a reference in the digitizing design for dental technicians



#### **High Precision**

AutoScan-DS200+ scanning precision is less than 0.015 mm. The margin line and surface of dies are quite sharp



## **High Efficiency**

Scanning time: full arch 6s; upper jaw / lower jaw 18; 1~8 teeth 20s; impression 80s

# **Specification**

	Model	AutoScan-DS200+
	Camera Resolution	1,300,000
	Accuracy	<0.015mm
	Scanning Range	100mm*100mm*75mm
		full arch 6s
	Scanning Time	upper jaw / lower jaw 18s
		1~8 teeth 20s
		impression 80s
	Scanning Principle	structured blue light 3D scanning
	Temperature	$10^{\circ}\text{C}\sim30^{\circ}\text{C}$ (higher temperature may affect the scanning result)
	Dimension	315mm*320mm*470mm
	Weight	20kg
	Output	STL, OBJ
	Interface	USB 3.0
	Power	AC 24V

Notice: More detailed information about the products, please visit our web for inquiry.

Email: sales@shining3d.com Tel: +86 571 82999050 Web: www.shining3d.com